



## HUMINATOR

high precision transportable humidity lab



- ▶ temperature control  
59°-104° F
- ▶ humidity range  
5-95% RH

- individually programmable
- easy to run menu
- graphic display
- RS-232 Interface





## Huminator

Using the HUMINATOR you can quickly and easily calibrate humidity measuring instruments, probes and data loggers from Testo and other companies. The HUMINATOR calibration system is a high-

performance, stand alone temperature/humidity reference generator. It features a thermal servo system to stabilize temperature in the range of 59 to 104°C. Relative Humidity is rapidly generated in the range

of 5 to 95%.

With the special Testo front panel of the chamber it is possible to calibrate 4 humidity probes at the same time. It is also possible to calibrate various data loggers.

Qty	Description	Part no.	Price
	Recommended set for the HUMINATOR: HUMINATOR incl. Testo sensor and 15 probe adapters	0519.0801	
	testo 650 2 channel reference temperature and humidity measuring instrument with pressure measurement	0563.6501	
	Mains unit for testo 650 110 VAC	0554.1085	
	Highly accurate reference humidity/temperature probe +1%RH accuracy	0636.9741	
	Plug-in head cable to connect probe to measuring instrument	0430.0143	
	DKD calibration measuring points: 11,3, 30, 50, 75,3, 90%RH at +25°C	0520.0216	
	Case for HUMINATOR	0519.0820	

Technical Data HUMINATOR	
Temperature range:	59 to 104 F
Humidity range:	5 to 95%RH
Power supply:	.85 to 264 VAC, 47 to 63 Hz
Interface:	.RS 232
Display:	.Grafical display
Dimension meas. chamber:	..... ca. 6 inches diameter
Dimension:	..... 19 inch rack
Accuracy:	..... Temperature 0.5 F (10-85%RH at 25°C) Humidity 2%RH (10-85%RH at 25°C)
Stability:	..... 0.2 F (10-85%RH at 25°C) ..... 1% RH (10-85%RH at 25°C)
Supplement:	.....drying container with drying reagent
Weight:	..... 32 lbs

### Your Testo-Partner:

- I would like to order the items as indicated above:
- Please contact me at the address below:

_____ <b>name</b>
_____ <b>company</b>
_____ <b>date, signature</b>